


DYNAPRO TIPMATIC

Planungshinweise/Installation information/Instructions de planification/Istruzioni per la progettazione/
Indicaciones de planificación/Installations information/Технические данные


113703 - 04/2017




Einbaumaße/Installation dimensions/Cotes de montage/Misure di montaggio/
Medidas de montaje/Installations mått/Установочные размеры





Schubkasten/Drawer/Tiroir/Cassetto/Cajón/Låda/Выдвижной ящик



Innenschub/Inset drawer/Tiroir interieur/Cassetto interno/Cajón interior/
Innerlåda/ Внутренний выдвижной ящик



Befestigungspositionen für Vollauszug/Fastening positions for full extension slide/Positions de fixation pour sortie totale/Posizioni di fissaggio per estrazione totale/
Posiciones de fijación para guía de extracción completa/Infästningspositioner för fullutdragsskena/Позиции для закрепления направляющих полного выдвижения



LEGENDE/LEGEND/LÉGENDE/LEGENDA/LEYENDA/FÖRKORTNINGAR/УСЛОВНЫЕ ОБОЗНАЧЕНИЯ

KV	Korpusvorderkante/Front edge of cabinet/Chant avant caisson/Fondo anteriore del mobile/Canto frontal del módulo/Framkant skåp/Передняя кромка корпуса
LWK	Lichte Weite Korpus/Inside cabinet width/Largeur intérieure caisson/Luce libera mobile/Ancho interior del módulo/Innerrmått skåp/Внутренняя ширина корпуса







LWS	Lichte Weite Schubkasten/Internal drawer width/Largeur intérieure tiroir/Luce libera cassetto/Ancho interior del cajón/Innerrmått låda/Внутр. ширина выдвижного ящика
MET	Mindesteinbautiefe/Minimum installation depth/Profondeur minimum de montage/Profondità minima d'incasso/Profundidad de montaje mínima/Minsta inbyggnadsdjup/Миним. установочная глубина

NL	Nennlänge/Nominal length/Longueur nominale/Lunghezza nominale/Longitud nominal/Nominell längd/Номинальная длина
SKL	Schubkastenlänge/Length of drawer/Longueur du tiroir/Lunghezza del cassetto/Longitud del cajón/Lådlängd/Длина выдвижного ящика

DYNAPRO TIPMATIC

Wichtige Hinweise/Important information/Informations importantes/Avvertenze importanti/Indicaciones importantes/
Viktig information/Важные примечания

113703 – 04/2017



Optionales Zubehör/Optional accessories/ Accessoires optionnels/Accessori opzionali/ Accesorios opcionales/Tillbehör/ Дополнительные опции Synchronisation/Synchronisation/Synchronisa- tion/Sincronizzazione/Sincronización/Synkroni- sation/Синхронизация  Synchro-Modul/Synchronisation module/ Module de synchronisation/Modulo di sincronizza- zione/Módulo de sincronización/Synkroniserings modul/Синхронизирующий модуль: F 134117475 (40kg) F 134117476 (60kg) Synchro-Stange/Synchronisation rod/Barre de liaison/Barra di sincronizzazione/Barra de sincronización/Synkroniserings stång/ Синхронизирующая штанга: F 134116947	< 700 mm 	> 700 mm 
Frontspalteinstellung/Front gap adjustment/ Réglage du jeu de façade/Regolazione del gioco frontale/Regulación de la fuga frontal/ Justering av front spalt/Регулировка зазора фасада	< 300 mm 	> 300 mm 
Transport/Transport/Transport/Trasporto/ Transporte/Transport/Транспортировка		

DYNAPRO TIPMATIC



Montage / Assembly / Montage / Montaggio / Montaje / Monteringsanvisning / Монтаж

113703 - 04/2017


1




2




3




4




5




6



7



8






DYNAPRO TIPMATIC


Verstellungen / Adjustment / Réglages / Regolazioni / Ajustes / Justering / Виды регулировки

113703 - 04/2017


Frontspalteinstellung / Front gap adjustment /
Réglage du jeu de façade / Regolazione del gioco
frontale / Regulación de la fuga frontal / Justering
av front spalt / Регулировка зазора фасада




Max. + 3.5 mm




Dynapro 3D





Dynapro 2D




Max. + 4.0 mm




Dynapro 3D/2D




Max. $\pm$ 1.5 mm




1




2



3



4



5

