


Works light must be min.80 cm max.115 cm.


LIFT FOR WARDROBE MOUNTING INSTRUCTION






4- Pull to oval profile front. Pull to front oval profile (IMAGE C).

5- Then, combine teles⊂ opic middle tube to pulling tube with caps by screwing (C-1).



6- Fit to pulling arm on T items chanel upon telescopic tube (IMAGE D).



7- Then you make right pulling arm and mechanism (IMAGE E).

You must check work of mechanism.

MOUNTING PARTS		
NO	PART NAME	PCS.
1	LIFT FRAME	2
2	OVAL PROFILE	2
3	SLIDE TUBE COVER	2
4	TELESCOPIC MIDDLE TUBE	1
5	PLASTIK T PART	1
6	PULLING ARM	1
7	CHIPBOARD SCREW 3,5x35	12
8	CHIPBOARD SCREW Ø8×65	2
9	BOLD M6×30	4
10	ALLEN KEY 4 mm	1
STOCK CODE: SMA27 IMAGE NO: RSM177		